



5.2 HueckTec novelties

5.2.1 CE marking via HueckTec

From version 3.7 Build 1340, the CE marking in accordance with EN 14351 for doors and window elements is available in HUECKTEC.

For this purpose, the classes of resistance to wind load, water tightness, and air permeability are derived from stored and tested standard elements. The coefficient of heat transmission and the radiation characteristics are determined and issued on the basis of the information entered in the element.

| | | | |
|--------------------------------------------------------------------------------------------------|---------------------------------------------------------|-------------------------------------|--------------|
| CE | | | |
| Eduard Hueck GmbH & Co. KG Loher Str. 9 58511 Lüdenscheid | | | |
| EN 14351 - 1: 2006 Fenster und Außentüren für die Anwendung im Wohnungs- und Nichtwohnungsbau | | | |
| Widerstandsfähigkeit gegen Winddruck | Prüfdruck: Rahmendurchbiegung: | Klasse Klasse | 3 C |
| Schlagregendichtheit | ungeschützt (A) | Klasse | 3A |
| Stoßfestigkeit | | | npd |
| Tragfähigkeit der Sicherheitsvorrichtungen | | | npd |
| Schallschutz | | R _{w,R} [dB] | 36 |
| Wärmedurchgangskoeffizient | | U ₀ [W/m ² K] | 1,7 |
| Strahlungseigenschaften | Gesamtenergiedurchlassgrad Lichtdurchlässigkeitsgrad | | 0,20 0,90 |
| Luftdurchlässigkeit | | Klasse | 2 |

5.2.2 Online seminar

11. Online-Seminar

Tipps und Tricks 2

Moderation: Holger Achermann, Thomas Balzer
Zielgruppe: Alle HUECK-TEC Anwender

am 09. Juni 2010
10:00 – 10:30 Uhr

Neu! Kostenlos für Hueck-Tec Nutzer!

From HueckTec update 3.7 Build 1340 of March 2010, we offer online seminars for HueckTec at irregular intervals. These online seminars focus on a special topic and have a time frame of 20 – 30 minutes. They help you to improve your HueckTec skills at your workplace.



Via a headset (headphone with microphone) you can hear the instructor. And, if required, questions can be asked via chat.

The users are informed on upcoming seminars in a newsletter displayed in HueckTec where they can also register immediately by entering their name and email address. Following the initial registration, you will receive a free HueckTec headset.

Shortly before the seminar, the participants will receive an email containing a link which provides access to the training.

If you wish to use this new function, the internet update system must be activated in HueckTec.

5.2.3 Generation of drawings

With its update version 3.7 Build 1340, HueckTec offers an extended representation of fittings. The fitting data are already shown upon entry, in the element views, in the lists and in the sectional views.

